

Rittal – The System.

Faster – better – everywhere.



PK 9511.000

Polycarbonate enclosures PK

State: 26.9.2024 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PK 9511.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.

Features

Model No.	PK 9511.000
Design	null
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 130 mm Height: 130 mm Depth: 99 mm
Operating temperature range	-35 °C...80 °C
Basic material	Polycarbonate
Packs of	4 pc(s).
Weight/pack	1,66 kg

Features

Net weight	1.464
Gross weight	1.64
Customs tariff number	94037000
EAN	4028177139374
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	C-UL DNV-GL UL UL + C-UL (listed)
-----------	--

Explanations	Declaration of conformity
--------------	---------------------------