

Rittal – The System.

Faster – better – everywhere.



PC 5366.350 PC enclosure system

State: 19/10/2024 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5366.350 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

Features

| | |
|---------------------|---|
| Model No. | PC 5366.350 |
| Design | with glazed door at the top, keyboard drawer, small mounting compartment and component shelf |
| Product description | Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access. |
| Material | Enclosure, door, rear door, mounting compartment, supports: Sheet steel Handles, decorative trim panels: Plastic Door trim panels: Aluminium Viewing window: Single-pane safety glass |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting compartment, support: powder-coated |
| General colour | RAL 7035 |
| Colour | Enclosure, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor panel, door centre part: RAL 7015 |
| Supply includes | Enclosure, door, rear door Gland plates Glazed door, top Mounting compartment, small Keyboard drawer Component shelf |
| Dimensions | Width: 600 mm Height: 1,600 mm Depth: 636 mm |

Features

| | |
|-------------------------------------|---|
| IP protection category to IEC 60529 | IP 55 |
| Protection category NEMA | NEMA 12 |
| Type rating to UL 50E | Type 1 Type 12 |
| Max. keyboard dimensions (WxHxD) | 480 x 70 x 260 mm |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Weight/pack | 95.5 kg |
| Net weight | 97.5 |
| Gross weight | 100 |
| PCF/PU (cradle-to-gate) | 363.9 kg CO2 eq (Cat B) |
| Note on the PCF class | Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared |
| EAN | 4028177959439 |
| ETIM 7.0 | EC002502 |
| ECLASS 8.0 | 27180501 |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Certificates | Surface finish |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

PC-Enclosure with glazed door, mounting compartment,
keyboard-drawer

Enclosure for stand-alone siting, consisting of solid body,
glazed door at the top, mounting compartment small,
Keyboard-drawer, compartment shelf, bottom door, rear door
and welded base assembly. Enclosure body with
profiled mounting angles at the front and rear,
sidewalls and rear. System slots on a 25 mm pitch pattern,
all around, for individual interior installation
and two pairs of mounting angles for
space-saving system installation.

Glazed door, top:

With support frame latched from the inside, right hinged
vertical decorative trim panels
pane with screen-printed mask

Mounting compartment, small:

Hinged on right-hand side,
at left-hand side screw-fastened from the inside,
installation plate folded, decorative side trim panels

Component shelf for monitor:

Perforated, fixed

Drawer for keyboard:

Housing with keyboard drawer plus pull-out mousepad
front trim panel with handle strip, folded as
handrest, with lock insert no. 3524 E

with unlocking device for glazed door, top

max. keyboard dimensions (WxHxD): 480x70x260 mm

Bottom door:

Vertical bars with locking rod and
double-bit insert, hinged on right-hand side
door resp. installation plate folded

Rear door:

With locking rod and double-bit insert,
hinged on right-hand side

With grand plates, divided

Material:

Enclosure, door, rear door, mounting compartment,
supports: sheet steel

Handles, decorative trim panels: Plastic

Door trim panels: Aluminium

Viewing window: Single pane safety glass

Gland plates: sheet steel, galvanized

Surface finish:

Enclosure and door: dipcoat primed, powder coated outside,

Textured paint

Mounting compartment, supports: powder coated

Colour:

Enclosure, door, decorative trim panels, supports: RAL 7035

Handles: RAL 7015

Monitor panel, door centre part: RAL 7015

Protection class:

IP to IEC 60 529: IP55

NEMA: NEMA 12

Dimensions WHD: 600 x 1600 x 636 mm

Model No.: 5366350

Manufacturer: Rittal GmbH & Co.KG