

# Rittal – The System.

Faster – better – everywhere.



## SV 9683.680

# Partial mounting plate

State: 26/09/2024 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9683.680 - Partial mounting plate for compartment side panel

With or without duct, for direct attachment to the functional space side panel.

## Features

Model No.	SV 9683.680
Design	Solid
Product description	For direct attachment to the compartment side panel for internal compartmentalisation. Universal interior installation with switchgear and controlgear. Creation of additional mounting levels. In combination with compartment dividers and side panel, internal compartmentalisation in accordance with Form 1 to 4 is possible.
Material	Sheet steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly parts
For compartment height	1,000 mm
Dimensions	Width: 702 mm Height: 993 mm
To fit	Width: = 800 mm
Packs of	1 pc(s).
Weight/pack	16 kg
Net weight	13.5
Gross weight	14.5
PCF/PU (Cradle-to-Gate)	61 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	73269098
EAN	4028177935198

# Features

---

ETIM 7.0	EC001900
ECLASS 8.0	27400613

---

# Approvals

---

Explanations	Declaration of conformity
	Declaration of conformity UK