


**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.130**

**Splitter hole punch, round**

State: 3/02/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.130 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

## Features

Model No.	AS 4055.130
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies
Maximum machinable material thickness, stainless steel	2.5 mm
Ø punch	30.5 mm
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	0.185
Gross weight	0.209
Customs tariff number	82073010
EAN	4028177808041
ETIM 9	EC000156
ETIM 8	EC000156
ECLASS 8.0	21049047