

Rittal – The System.

Faster – better – everywhere.



AS 4055.560

Splitter hole punch, round

State: 19/10/2024 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.560 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.560
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	60 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Weight/pack	0.836 kg
Customs tariff number	82073010
EAN	4028177808805
ETIM 7.0	EC000156
ECLASS 8.0	21049047