

Rittal – The System.

Faster – better – everywhere.



WM 1034.250

WM wall-mounted enclosure

State: 4/25/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 1034.250 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 1034.250
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert
Dimensions	Width: 300 mm Height: 400 mm Depth: 210 mm Width: 11.8 " Height: 15.7 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	254 mm x 375 mm 10 " x 14.8 "

Features

Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
--------------------------	--

Material thickness - door	1.5 mm 0.06 "
---------------------------	------------------

Material thickness - enclosure	1.5 mm 0.06 "
--------------------------------	------------------

Material thickness – mounting plate	1.5 mm 0.06 "
-------------------------------------	------------------

Packaging unit	1 pc(s).
----------------	----------

Net weight	18.43
------------	-------

Gross weight	19.4
--------------	------

Customs tariff number	7326908688
-----------------------	------------

EAN	4028177532670
-----	---------------

UPC-Code	83106
----------	-------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Explanations	Declaration of conformity
--------------	---------------------------
