

Rittal – The System.

Faster – better – everywhere.



WM 1077.250

WM wall-mounted enclosure

State: 4/25/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 1077.250 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 1077.250
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert
Dimensions	Width: 760 mm Height: 760 mm Depth: 210 mm Width: 29.9 " Height: 29.9 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	704 mm x 730 mm 27.7 " x 28.7 "

Features

Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
--------------------------	--

Material thickness - door	2 mm 0.08 "
---------------------------	----------------

Material thickness - enclosure	1.5 mm 0.06 "
--------------------------------	------------------

Material thickness – mounting plate	2.5 mm 0.1 "
-------------------------------------	-----------------

Packaging unit	1 pc(s).
----------------	----------

Net weight	83.333
------------	--------

Gross weight	87.743
--------------	--------

Customs tariff number	7326908688
-----------------------	------------

EAN	4028177532724
-----	---------------

UPC-Code	83112
----------	-------

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Explanations	Declaration of conformity
--------------	---------------------------
