

# Rittal – The System.

Faster – better – everywhere.



## SK 3171.100 Fleece filter mat

State: 7/3/2024 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3171.100 - Fleece filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

## Features

Model No.	SK 3171.100
Version	for filter fans
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibers
Note	Not suitable for use in EMC filter fans.
Suitable for Model No.	3239....
Dimensions	Width: 173 mm Height: 173 mm Depth: 17 mm Width: 6.81 " Height: 6.81 " Depth: 0.67 "
Filter class	to DIN EN 779: G3 to DIN EN ISO 16890: ISO coarse 50%
Weight/package unit	0.05 kg 0.1 lb.
Packaging unit	5 pc(s).
Customs tariff number	56039390
EAN	4028177038059
E-Number Sweden	E3404740
ETIM 8	EC002513
ETIM 7.0	EC002513

# Features

---

ECLASS 8.0

27180706

# Approvals

---

Approvals

UR + C-UR (recognized)

Certificates

EAC