

Rittal – The System.

Faster – better – everywhere.



SK 3239.200 Outlet Filters

State: 7/23/2024 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3239.200
Product description	For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.
Material	ABS
Color	RAL 7035
Supply includes	Outlet Filters Fleece filter mat
Mounting cut-out	Width of opening: 177 mm Cut-out height: 177 mm Width of opening: 6.97 " Cut-out height: 6.97 "
Suitable for Model No.	SK 3239.1xx
Dimensions	Width: 204 mm Height: 204 mm Depth: 24 mm Width: 8.03 " Height: 8.03 " Depth: 0.94 "
Protection category NEMA	Type 12 with fleece filter/folded filter Type 3, 3R, 4, 4X with fleece filter/folded filter and hose-proof hood

Features

Protection category IP to IEC 60529	IP54 with fleece filter/folded filter IP55 with folded filter and absorber mat IP56 with fleece filter/folded filter and hose-proof hood
Weight/package unit	0.38 kg 0.8 lb.
Packaging unit	1 pc(s).
Customs tariff number	39269097
EAN	4028177651852
E-Number Sweden	E3404360
ETIM 8	EC002513
ETIM 7.0	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	CSA UL + C-UL - FTFA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity
