

# Rittal – The System.

Faster – better – everywhere.



## SZ 4139.180 Courtesy light

State: 9/29/2024 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4139.180 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

## Features

Model No.	SZ 4139.180
Version	without door-operated switch
Supply includes	Courtesy light Light (bulb) Light cover Assembly components
Rated power	18 W
Ballast	Wide range voltage EB
Connection options	Power supply through connector Door-operated switch Through-wiring (configuration of row of luminaires)
Light (bulb)	Fluorescent lamp, G13 backplate
Protection category	I (PE conductor)
Switch (type)	Integral, on/off/door-operated switch mode
Light cover	Yes
Light – installation type	Screw fastening
Rated impulse withstand voltage, phase to earth	1000 V AC
Rated impulse withstand voltage, phase to phase	500 V AC
Rated insulation voltage	500 V DC/1s
Installation options	TS horizontal profile from roof frames: direct TS, SE vertical section: with TS adapter bracket SE sections on front and rear of roof frame: with TS adapter bracket SE profiles to the side of roof frames: direct AE, CM, TP: with universal bracket AE: with rail for interior installation

# Features

---

Dimensions	Width: 682 mm Height: 117 mm Depth: 50 mm Width: 26.9 " Height: 4.61 " Depth: 1.97 "
Operating temperature range	-15 °C...45 °C 5 °F...113 °F
Outlets	D, ground contact (type F, CEE 7/4)
Storage temperature range	-20 °C...70 °C -4 °F...158 °F
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Socket version	D, ground contact (type F, CEE 7/4)
Packaging unit	1 pc(s).
Weight/packaging unit	2.32 kg 5.1 lb.
Net weight	1.55
Gross weight	1.8
Customs tariff number	94054990
EAN	4028177092341
ETIM 7.0	EC000321
ECLASS 8.0	27189241

---

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---