

Rittal – The System.

Faster – better – everywhere.

▶ 316 Stainless Steel TS 8 Enclosure



Rittal is proud to offer the latest addition to its world recognized enclosure portfolio: the 316 Stainless Steel TS 8. Based on the original highly acclaimed TS 8 enclosure series, this rugged stainless steel platform from the world's leading enclosure manufacturer is the ideal freestanding solution for harsh environments.

This UL Type 4X modular enclosure affords many advantages over traditional unibody designs including expandability, lower weight (less transportation costs), more mounting space, and better workability (less labor costs). Whether housing drives, flow monitoring systems, or critical electrical components, the 316 Stainless Steel TS 8 maintains a clean, consistent environment in extreme locations.

The 316 Stainless Steel TS 8 features and benefits include:

- 30 percent more available mounting space than traditional unibody enclosures of equal dimensions
- Four-point latching system and continuous foamed-in-place gasket that provide a water and dust proof environmental seal
- Padlock-able handle that provides both easy access and security
- Spring-loaded quick release hinges
- Full functionality and expandability of the TS enclosure series
- Large assortment of accessories for three dimensional mounting of components on all internal surfaces
- Internally removable floor panel that simplifies conduit and wiring installation



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

www.rittal.us

316 Stainless Steel TS 8 Enclosure




316 stainless steel four-point latching system and continuous foamed-in-place gasket provides a water and dust proof environmental seal




Padlock-able 316 stainless steel handle provides both easy access and security



Note: Cabinet sidewalls are purchased as a separate item to complete assembly.



316 stainless steel gland plate provides easy conduit/cable installation



A floor stand kit permits easy access to the bottom of the enclosure. Purchased separately

316 Stainless Steel TS8 Enclosure, UL Type 4X, IP 66, Single Door — Type 316 Stainless Steel

Part Number	HxWxD inches	HxWxD mm	Sidewalls Part Number (Pair)	Mounting Panel (Included) HxW inches	Mounting Panel (Included) HxW mm	8" (200 mm) High Plinth, Front & Rear	8" (200 mm) High Plinth, Sides	12" (300 mm) High Floor Stand Kit
9977477	71x24x24	1800x0600x0600	9977479	67x20	1696x499	9972908	8702065	9963530
9977472	71x32x20	1800x0800x0500	9977478	67x28	1696x699	9972907	8702055	9963529
9977475	71x32x24	1800x0800x0600	9977479	67x28	1696x699	9972907	8702065	9963530
9977470	79x24x24	2000x0600x0600	9977481	75x20	1896x499	9972908	8702065	9963530
9977473	79x24x32	2000x0600x0800	9977482	75x20	1896x499	9972908	9977494	9973052
9977468	79x32x20	2000x0800x0500	9977480	75x28	1896x699	9972907	8702055	9963529
9977467	79x32x24	2000x0800x0600	9977481	75x28	1896x699	9972907	8702065	9963530
9977466	79x32x32	2000x0800x0800	9977482	75x28	1896x699	9972907	9977494	9973052
9977471	87x24x24	2200x0600x0600	9977483	83x20	2096x499	9972908	8702065	9963530
9977476	87x24x32	2200x0600x0800	9977484	83x20	2096x499	9972908	9977494	9973052
9977469	87x32x24	2200x0800x0600	9977483	83x28	2096x699	9972907	8702065	9963530
9977474	87x32x32	2200x0800x0800	9977484	83x28	2096x699	9972907	9977494	9973052

Rittal Corporation

Woodfield Corporate Center • 425 N. Martingale Road, Suite 400 • Schaumburg, IL • USA
 1 Rittal Place • Urbana Ohio 43078 • USA
 Phone: 937-399-0500 • Toll-free: 800-477-4000
 Email: rittal@rittal.us • Online: www.rittal.us

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

06/16 • US286