



Rittal – The System.

Faster – better – everywhere.

Rittal Fan Shrouds

Rittal offers a complete line of fan shrouds. From our standard carbon steel Type 3R/4 units or stainless steel Type 4X rated units to be used in harsh locations – we have a shroud to meet the most stringent applications.

Our Hi-Visibility blue silicone gasket quickly identifies the seal meets FDA Guideline 21 CFR 177.2600. Additionally, the material allows easy cleaning in food and beverage environments.



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Stainless Steel

For filter fan/ outlet filter	Dimensions H x W x D inches (mm)	Part No.
3237. . . .	9.1 x 5.9 x 1.6 (230 x 150 x 40)	3237.080
3238. . . .	9.6 x 6.9 x 2.2 (245 x 176 x 55)	3238.080
3239. . . .	13 x 9.2 x 2.2 (330 x 233 x 55)	3239.080
3240. . . ./3241. . . .	15.3 x 11.1 x 3.3 (390 x 282 x 85)	3240.080
3243. . . ./3244. . . .	18.9 x 13.4 x 4.3 (480 x 350 x 110)	3243.080
3245. . . .	18.9 x 13.4 x 6.3 (480 x 350 x 160)	3245.080

UL Protection Category:


- 3237, 3245: Type 12, 3R
- 3238, 3239, 3240, and 3243: Type 12, 3, 3R, 4, and 4X

Carbon Steel, RAL 7035

For filter fan/ outlet filter	Dimensions H x W x D inches (mm)	Part No.
3237. . . .	9.1 x 5.9 x 1.6 (230 x 150 x 40)	3237.085
3238. . . .	9.6 x 6.9 x 2.2 (245 x 176 x 55)	3238.085
3239. . . .	13 x 9.2 x 2.2 (330 x 233 x 55)	3239.085
3240. . . ./3241. . . .	15.3 x 11.1 x 3.3 (390 x 282 x 85)	3240.085
3243. . . ./3244. . . .	18.9 x 13.4 x 4.3 (480 x 350 x 110)	3243.085

UL Protection Category:

- 3237: Type 12, 3R
- 3238, 3239, 3240, and 3243: Type 12, 3, 3R, and 4



You can find the contact details of all Rittal companies throughout the world here.



www.rittal.com/contact

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

