

RITTAL GMBH & CO. KG

Auf dem stützelberg
D-35745 Herborn
<http://www.rittal.de>



Modell/model :SK3319.61X
:RITA10140.02 - MINI0015MH V000 - S993 - V412
Zeichnungsnummer/drawing number:EFB0398 -

Einspeisung/power supply :230 1 50-60
Kältemittel / refrigerant :R134a

Kunde/customer :
Reference :


Erstellt am/created the :10. Dic. 2010 by MV1 Anzahl blätter/highest page nbr.: 5
Geändert/changed on the : by Blatt/number of page : 1


Inhaltsverzeichnis / Page overview

PAGRIT1 23.01.2006

Seite	Beschreibung	Date revision	Geändert
1	COVER	10. Dic. 2010	MV1
2	INHALTSVERZEICHNIS / PAGE OVERVIEW	30. Mag. 2014	FF2
3	REFRIGERATION CIRCUIT	30. Mag. 2014	FF2
4	HYDRAULIC CIRCUIT	30. Mag. 2014	FF2
5	BILL OF MATERIAL	30. Mag. 2014	FF2








Bill of materials

RICKE1 11.07.2003

Item designation	Amount	Um	Article number	Designation	Manufacturer	Internal number	P/P
B1	1	ST	K014001A/2	PROBE-TEMP NTC ITALCOPPIE NTC016HPOR	CAREL	908957	3. 4
B2	1	ST	NTC007HPOR	PROBE-TEMP NTC CAREL NTC007HPOR	CAREL	903071	3. 3
B3	1	ST	NTC007HPOR	PROBE-TEMP NTC CAREL NTC007HPOR	CAREL	903071	3. 4
B4	1	ST	NTC007HPOR	PROBE-TEMP NTC CAREL NTC007HPOR	CAREL	903071	3. 4
BC	1	ST	DISA1085CH	HEX F-TUB CN 2522C0 10 4 25 520 1 A10S	HTS HEAT TRANSFER SYSTEMS	910866	3. 3
FI	1	ST	023Z4821	FILTER DEIDR DANFOSS DML032S	DANFOSS	219016	3. 0
FL	1	ST	VK308MORITTA02	FLOWSWITCH SIKA VK308MORITTA02 1/4"	SIKA SYSTEMTECHNIK	902023	4. 2
M1	1	ST	SC156H-AB	COMPRESSOR ALTERNATIVE DANFOSS SC156H-AB	DANFOSS	219822	3. 6
M2	1	ST	K4E250-AA04-11	FAN AXIAL EBM K4E250-AA04-11	EBMPAPST SRL	270179	3. 4
M3	1	ST	K4E250-AA04-11	FAN AXIAL EBM K4E250-AA04-11	EBMPAPST SRL	270179	3. 3
M4	1	ST	Y-2951.0328	SPECK PUMP Y-2951.0328	SPECK PUMPENFABRIK GMBH & CO	915984	4. 2
PA	1	ST	061F3069	PRESSHP DANFOSS PSAH FIX 23-17	DANFOSS	902390	3. 7
PHE	1	ST	6A-M18-14-L162	HEX PLATE 6EA M18-14-L162	6EA ECOBRAZE AB	909203	3. 3
TS	1	ST	RITM230T00	TEMP-CONTR CAREL RITM230T00	CAREL	901282	3. 8
TS	1	ST	RITCUSRON1	TEMP-CONTR DISPLAY CAREL RITCUSRON1	CAREL	315939	3. 8
TS	1	ST	RITCCON151	TEMP-CONTR ACCESS MGE RITCCON151	CAREL	258218	3. 8
VA	1	ST	DISA1984CL	CAR TANK 120x192x196 PP 2,5L	ZF SAS DI FROLA	901442	4. 4
VT	1	ST	RF6B04-0.44-41	VALVEXP TERMOSTAT SANHUA RF6B04-0.44-41	SANHUA	338651	3. 2

4

Created by MV1 on the 10. Dic. 2010	 RITTAL GmbH & Co. KG	SK3319.61X RITA10140.02 - MINI0015MH V000 - S993 - V412 BILL OF MATERIAL	Drawing number	=	Eplan 5.70.4
Last revision by on the			EFB0398	+	CARTRITFLU 23.01.2006
			Kaltemittel / Refrigerant		5
			R134a		5