

# Rittal – The System.

Faster – better – everywhere.



## DK 5501.805

# Air baffle plates for TS IT 482.6 mm (19") mounting angles

State: 26/09/2024 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.805 - Air baffle plates for TS IT 482.6 mm (19") mounting angles

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

|                      |                                                                                                                                                                                                                                                      |
|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.            | DK 5501.805                                                                                                                                                                                                                                          |
| Product description  | With all-round brush strip for collision-free shielding with installed bar systems on the outer mounting level.                                                                                                                                      |
| Applications         | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.                                                                                                                                               |
| Material             | Sheet steel<br>Blanking panel: Plastic, UL 94-HB, halogen-free<br>Brush strip: Plastic, UL 94-HB                                                                                                                                                     |
| Surface finish       | Spray-finished                                                                                                                                                                                                                                       |
| Colour               | RAL 9005                                                                                                                                                                                                                                             |
| Supply includes      | 2 vertical trim panels<br>2 horizontal trim panels<br>4 brush strips<br>4 cellular PU foam pieces<br>Assembly parts                                                                                                                                  |
| Assembly instruction | The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.<br>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles. |

# Features

|                       |                                   |
|-----------------------|-----------------------------------|
| To fit                | Width: 600 mm<br>Height: 2,000 mm |
| Packs of              | 1 pc(s).                          |
| Weight/pack           | 4.85 kg                           |
| Net weight            | 4.65                              |
| Gross weight          | 4.85                              |
| Customs tariff number | 73269098                          |
| EAN                   | 4028177679177                     |
| E-Number Sweden       | E7239698                          |
| ETIM 7.0              | EC000331                          |
| ECLASS 8.0            | 27189272                          |

## Tender text

### Air baffle plate

Air baffle plate to separate hot/cold zones within an enclosure or complete enclosure suites.

An all-round brush strip ensures collision-free shielding with installed bar systems on the outer mounting level.

Tool-less mounting on the mounting angles of the 482.6 mm (19") level via quick-action fastener or screw-fastened as an option.

May be used, for example for Rittal enclosure series TS IT.

For enclosure (WxH) 600x2000 mm.

Material: Air baffle plates, sheet steel,

Brush strips: Plastic UL 94- HB

Model No. DK: 5501.805

Manufacturer: Rittal