

# CERTIFICATE

issued by

## Rittal GmbH & Co. KG

Auf dem Stützelberg  
D-35745 Herborn

Quality Management

**Herewith we confirm that the Rittal VX IT standard 19" mounting angles and depth struts have a static load capacity of 12.000 N (UL 2416 1.Ed. 2015-03-11) and 15.000N (EN 62368-1:2016-05) under following conditions:**

- Only static load permitted.
- No inclination permitted. The rack must stand horizontal and even.
- The mounting angles must be fixed to the depth struts with minimum 2 screws on each ending
- The load of each component must be evenly distributed over the whole area and fixed with all mounting angles (for example with screws and captive nuts) directly after loading, which has to be done from bottom to the top.
- The front mounting angles should have a distance to the front of the VX frame of max. 150mm
- At a depth greater than 1000 mm one punched rail must be mounted rectangular under the depth struts of the 800mm wide racks. The rail should be fixed with one screw per depth strut in the hole with the lowest distance to the front 19"- mounting angles

Herborn, 2021-05-19



Christian Haim  
Quality Management Laboratory

Rittal GmbH & Co. KG  
Personally liable:  
Rittal Management GmbH,  
Schwende

Rittal GmbH & Co. KG  
Auf dem Stützelberg  
D-35745 Herborn  
Phone: +49(0)27 72 5 05-0  
Fax: +49(0)27 72 5 05-23 19  
E-Mail: info@rittal.de  
www.rittal.de  
HRA 6126 Wetzlar

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

