










PLS busbar systems

up to 800/1600A

<p>Technical information for the calculation of rated currents to DIN 43 671, see chapter 2-102, page 1/2</p> <p>Note: – UL approval only applies in conjunction with AC application</p> <p>Approvals:  US LISTED E191125</p>						
	For Rittal system	PLS 800		PLS 1600		PLS 1600 PLUS
	Number of poles	3-pole		3-pole		4-pole
	Bar centre distance mm	60		60		60
	Rated operating voltage	IEC	1000 V AC	1000 V AC	1000 V AC	1000 V AC
	UL	–	1500 V DC	–	–	
		–	600 V AC	–	600 V AC	
For application		IEC	IEC/UL	IEC	IEC/UL	
Model No. SV		9341.000	9341.050¹⁾ 	9342.000	9342.050¹⁾ 	9342.004¹⁾ 
Tightening torque Nm						
– Assembly screw M6 x 16		5	5	–	–	
– Assembly screw M6 x 25		–	–	5	5	
– Busbar anti-slip guard		0.7	0.7	0.7	0.7	
– Cover attachment		–	–	–	–	

¹⁾ The use of a base tray is required for UL applications