

# Rittal – The System.

Faster – better – everywhere.



## DK 7320.721 Handles, electromagnetic

State: 27/09/2024 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7320.721 - Handles, electromagnetic for CMC III and IoT Interface

Handles may be integrated into various enclosure systems.

## Features

Model No.	DK 7320.721
Design	Comfort handle:with master key function
Product description	For control and monitoring via a central CMC III type control unit and IoT interface.
Colour	RAL 7035
Supply includes	2 adaptors for glazed door Cable clamps Adaptor for profile half-cylinders Connection cable (3 m) with RJ 12 connector Assembly parts
Lock type	Master key function (with emergency open function)
Rated current max.	0.1 A
No. of participants per IoT interface (max.)	16
No. of participating PU compact (max.)	2
No. of participating PU (max.)	16
Number subscribers per PDU note	Max. 5 p. for power supply with PoE
Packs of	1 pc(s).
Weight/pack	1.084 kg
Net weight	0.99
Gross weight	0.992
Customs tariff number	83024110
EAN	4028177390386

# Features

---

ETIM 7.0	EC000327
ECLASS 8.0	27409217

---

# Approvals

---

Explanations	Manufacturer's declaration Declaration of conformity
--------------	---

# Tender text

Comfort handle for TS 8 with master-key function,,,,,,,,,,,,,  
The TS 8 handle includes the master key function.  
This means that, independently of the control system,  
the handle can always be opened using the master-key.  
The door can be released via the CMC-TC system.  
In addition an access unit (V1.1) and an access sensor  
(7320.530) should be used so that the door status can  
be polled.

Technical specifications:

Rated voltage: 24 V DC  
Rated current: max. 100 mA  
Connection cable: Length 3 m, RJ 12 connector  
Connection cable: Length 2 m, RJ 12/RJ 12 connector  
Extension coupling: RJ 12/RJ 12 jack  
Temperature application range: +5°C to +40°C  
Protection category: IP 40