

# Rittal – The System.

Faster – better – everywhere.



## SK 3302.110

# Wall-Mounted Cooling Unit TopTherm Blue e

State: 2024-09-08 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3302.110 - Wall-Mounted Cooling Unit TopTherm Blue e 1023.64 - 13,648.6 BTU/h

Energy efficient Blue e wall mounting cooling units in performance classes 1023.64 to 13648.57 BTU/h, and with integrated electrical condensation evaporation for 3412.14 BTU/h and above. Available in the special formats “horizontal” and “flat”.



## Features

Model No.	SK 3302.110
Version	wall-mounted
Product description	Energy efficient Blue e wall-mounted cooling units in performance classes 300 W to 4000 W and with integrated electrical condensation evaporation for 1000 W and above.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners
Total cooling output to DIN EN 14511	Cooling output L35 L35/60 Hz: 0.34 kW Cooling output L35 L50/60 Hz: 0.21 kW
Rated operating voltage	115 V, 1~, 60 Hz
Rated current max.	At 60 Hz: 3.3 A

# Features

Start-up current (max.)	At 60 Hz: 8 A
Air throughput (unimpeded air flow)	External circuit: 310 m <sup>3</sup> /h Internal circuit: 345 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 60 Hz: 1.1
Version	wall-mounted
Dimensions	Width: 280 mm Height: 550 mm Depth: 140 mm
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit, IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.1 kg Global Warming Potential (GWP): 1,430 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.14 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	30 °C...55 °C
Rated power Pel	Rated power L35 L35/60 Hz: 0.31 kW Rated power L35 L50/60 Hz: 0.36 kW
Permissible operating pressure (p. max.)	25 bar
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packaging unit	1 pc(s).
Weight/packaging unit	13 kg
Customs tariff number	84158200
EAN	4028177322813
ETIM 8	EC000855

# Features

---

ETIM 7.0	EC000855
----------	----------

---

ECLASS 8.0	27180704
------------	----------

# Approvals

---

Approvals	UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--

---

Certificates	EAC
--------------	-----

---

Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
--------------	---