

# Rittal – The System.

Faster – better – everywhere.



## SK 3311.391 Liquid Cooling Package

State: 2024-10-19 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3311.391 - Liquid Cooling Package LCP Inline DX, UL

Open loop in row direct expansion cooling unit efficiently maintains proper server inlet temperatures.

## Features

Model No.	SK 3311.391
Benefits	<p>Maximum energy efficiency due to EC fan technology and IT-based control</p> <p>Minimal pressure loss at the air end, which in turn minimizes the power consumption of the fans</p> <p>Temperature monitoring and control.</p> <p>Redundant temperature sensor integrated at the air end</p> <p>Minimal area load due to low weight</p> <p>Absorbed thermal energy is emitted to the ambient air at the external condenser location, without heating up the installation room</p> <p>Ideal for IT cooling of small and medium-sized locations</p> <p>One or two racks can be cooled separately</p> <p>Due to the speed-regulated compressor, the cooling output adapts to the actual requirements</p> <p>Special maintenance of the LCP DX due to separation of cooling and server enclosures</p>
Function principle	LCP for use within a bayed enclosure suite. Hot air is drawn in from the aisle at the rear of the device, cooled by the high-capacity compact impellers, and blown back into the room or cold aisle after cooling
Color	RAL 9005
Max. cooling output	20 kW
Duty cycle	100 %
Type of connection (electrical)	Connection clamp
Cooling medium	R410A
EC fan	Yes

# Features

---

Fans may be exchanged with the system operational	Yes
Temperature control	Infinitely variable fan control Inverter-controlled compressor
Note	Ethernet cable 2482.720 required with SNMP network card 3311.320
Installation in bayed enclosure suite	Flush
Air throughput (unimpeded air flow)	At 50 Hz: 4,800 m <sup>3</sup> /h
Dimensions	Width: 300 mm Height: 2,000 mm Depth: 1,200 mm
Modulation range	6 - 20 kW
Operating temperature range	15 °C...35 °C
Storage temperature range	-20 °C...60 °C
Total cooling output/number of fan modules	20 kW
Packaging unit	1 pc(s).
Weight/packaging unit	201 kg
EAN	4028177940475
UPC-Code	91365
ECLASS 8.0	27180712

# Approvals

---

Approvals	UL
-----------	----