

**Rittal – The System.**

Faster – better – everywhere.



**AS 4055.137**

**Round split plate punching machine**

State: 2024-09-26 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.137 - Round split plate punching machine For stainless steel, with 3-way pitch

For punching round cut-outs

## Features

Model No.	AS 4055.137
Version	With 3-way split
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Die Stamp
Max. material thickness that can be machined for stainless steel	2.5 mm
Ø hole punch	37 mm
Note	Tension screws with a ball bearing must be used when operating with a wrench
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 55 mm
Hydraulic tension screw Ø	19 mm
Packaging unit	1 pc(s).
Weight/packaging unit	0.311 kg
Net weight	0.311
Gross weight	0.343
Customs tariff number	82073010
EAN	4028177808072
ETIM 8	EC000156
ETIM 7.0	EC000156

# Features

---

ECLASS 8.0

21049047