

# Rittal – The System.

Faster – better – everywhere.



## DK 7507.110 FlatBox

State: 2024-09-27 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7507.110 - FlatBox

Flat-packed enclosure. For optimal access and flexible use as a wall-mounted or floor-standing enclosure.

## Features

Model No.	DK 7507.110
Version	with 19" mounting rails
Product description	For flexible use as a wall-mounted or floor-standing enclosure.
Benefits	Tool-free quick mounting System accessories on the open 19" frame
Material	Carbon steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	RAL 7035
Supply includes	Flat-packed enclosure 1 wall section 2 basic supports 2 roof/base plates, with cut-outs for cable entry via brush strips 2 side panels, lockable 1 glazed door, lockable, security lock 3524 E, door catch freely selectable Connection components for tool-free, fast assembly Grounding kit for system-compatible grounding of all enclosure parts 19" profile rails
Height units	9 U
Dimensions	Width: 600 mm Height: 492 mm Depth: 600 mm
Installation height for components	9 U
Load capacity	max. 450 N

# Features

Note	Max. installation depth: Depth - 58 mm to rear panel Max. distance between two 19" levels: Depth - 104 mm The door opening angle is max. 210°
Base material	Carbon steel
Packaging unit	1 pc(s).
Weight/packaging unit	27 kg
Net weight	25.65
Gross weight	27
PCF/PU (Cradle-to-Gate)	102.9 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	94032080
EAN	4028177551442
E-Number Sweden	E7238402
ETIM 8	EC002500
ETIM 7.0	EC002500
ECLASS 8.0	27180208

# Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------