


# Rittal – The System.

Faster – better – everywhere.



## DK 7859.000 IT LED system light

State: 2024-10-19 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7859.000 - IT LED system light for IT enclosure systems and IT enclosures

For perfect illumination of IT enclosure systems and IT enclosures.

## Features

Model No.	DK 7859.000
Version	Insulated with internal fuse (T2A)
Product description	For optimum illumination of a network enclosure.
Benefits	Manual or automatic switching via door contact switch possible Optimum illumination of the entire enclosure Plug & play quick assembly Option of clip-on, screw or magnetic attachment Immediately ready for use due to plug-in connection cable Attachment with no loss of height units.
Material	Light body: Extruded aluminum Light cover: polycarbonate Light ends: PC-ABS
Color	Enclosure: RAL 7016
Supply includes	IT LED system light Magnet mounting kit Assembly screws
Connection options	Power supply through connector Door-operated switch
Protection category	II (total insulation)
Switch (type)	Integral, on/off/door-operated switch mode
Light – installation type	Screw fastening Clip fastening Magnet fastening

# Features

Installation options	Screw or clip directly to the VX IT/VX SE profile TE 8000, IT enclosure: with magnet mounting kit AX, TP: with magnet fastening kit AX: with rail for interior installation For operating with a CEE 7/16 Euro-plug or a chiller plug
Luminous flux	600 lm
Light color	4000 K (neutral white)
Note	The plug-in connection cables can only be used with the IT LED system lights Cascading multiple LED IT system lights is not possible
Dimensions	Width: 337 mm Height: 55 mm Depth: 23 mm
Operating temperature range	-20 °C...55 °C
Protection category IP to IEC 60529	IP 20
Packaging unit	1 pc(s).
Weight/packaging unit	0.35 kg
Net weight	0.38
Gross weight	0.401
Customs tariff number	94054990
EAN	4028177817937
ETIM 7.0	EC000321
ECLASS 8.0	27189241

# Approvals

Approvals	UL
Explanations	Declaration of conformity