

# Rittal – The System.

Faster – better – everywhere.



## TE 7888.532

## Network enclosure TE 8000

State: 2024-09-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TE 7888.532 - Network enclosure TE 8000

TE 8000 IT enclosure with glazed door, designed for individual interior installation.

## Features

Model No.	TE 7888.532
Version	without side panels
Benefits	No frame structure Optimum accessibility Easily installed Interchangeable door catch
Material	Carbon steel Viewing door: Single-pane safety glass, 3 mm
Surface finish	Mounting frame: Dipcoat-primed Enclosure panels: Powder-coated
Basic color	RAL 7035
Color	RAL 7035
Supply includes	Self-supporting 482.6 mm (19") mounting frames, front and rear, depth-variable Glazed door at the front, incl. 130° hinge, design handle and security lock 3524 E Carbon steel door at the rear, including 130° hinge, security lock 3524 E Base frame with maximum cut-out (for optional populating with module plates) Roof plate, incl. concealed cut-out for cable entry and optional fan 4 leveling feet, M10 (supplied loose) 4 spacers, 20 mm, to raise the roof (supplied loose) Baying kit
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Height units	42 U
Height units	42 U

# Features

---

Mounting space to 19" level, front/ rear	130 mm / 130 mm /
---	-------------------

---

Distance between levels as delivered	495 mm
---	--------

---

Load capacity	4,000 N
---------------	---------

---

Protection category IP to EN 60 529	IP 20
--	-------

---

Base material	Carbon steel
---------------	--------------

---

Packaging unit	1 pc(s).
----------------	----------

---

Weight/packaging unit	93 kg
-----------------------	-------

---

Net weight	90.25
------------	-------

---

Gross weight	93
--------------	----

---

EAN	4028177801479
-----	---------------

---

E-Number Sweden	E7282503
-----------------	----------

---

ETIM 7.0	EC002499
----------	----------

---

ECLASS 8.0	27180207
------------	----------

---

# Approvals

---

Explanations

Declaration of conformity