

Rittal – The System.

Faster – better – everywhere.



WM 8018.976

WM wall-mounted disconnect enclosure

State: 2024-09-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8018.976 - WM wall-mounted disconnect enclosure

These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8018.976
Product description	These flange mount disconnect wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.
Material	Door: Carbon steel, 2.0 mm, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel, zinc-plated
Surface finish	Dipcoat-primed and powder-coated, textured paint
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Flange door with universal disconnect cutout 2-point latching L-Handle
Dimensions	Width: 550 mm Height: 500 mm Depth: 210 mm

Features

Dimensions of mounting plate (W x H)	449 mm x 475 mm
Protection category NEMA	NEMA 4 UL Type 4/3R/12
Material thickness - door	2 mm
Material thickness - enclosure	2 mm
Material thickness – mounting plate	2.5 mm
Packaging unit	1 pc(s).
Weight/packaging unit	22 kg
Net weight	88.999
Gross weight	88.999
Customs tariff number	7326909099
UPC-Code	85753

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity