

Rittal – The System.

Faster – better – everywhere.



SV 9340.400 OM adapter

State: 2024-09-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.400 - OM adapter with Connection Cables



Features

| | |
|---|---|
| Model No. | SV 9340.400 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Color | Chassis: RAL 7035 |
| Connection cables (AWG) | AWG 12 |
| Rated current max. | 25 A |
| Rated operating voltage | 690 V, 3~ |
| Electrical UL ratings (SCCR) | 30 kA - 600 V, fuse class K5 max. 60 A, JDDZ/7 50 kA - 600 V, fuse class K5 max. 35 A, JDDZ/7 65 kA - 600 V, fuse class J max. 30 A, JDDZ/7 65 kA - 600 V, fuse class K5 max. 30 A, JDDZ/7 50 kA - 480 V, Combination Motor Controller max. 27 A, NKJH/7 65 kA - 480 V, Combination Motor Controller max. 32 A, NKJH/7 |
| For bar systems with center-to-center spacing | 60 mm |
| Length of connection cable | 130 mm |
| Support rail type | TS 45D TS 45D-V |
| Note | The technical data may vary for UL applications. |
| Number of poles | 3-pole |

Features

| | |
|------------------------------|--------------------------------|
| Dimensions | Width: 90 mm Height: 208 mm |
| Support rails Qty/height | 3 / 10 mm |
| Suitable for busbars | Height: 5, 10 mm |
| Support frame (W x H) | 45 mm x 170 mm |
| Packaging unit | 1 pc(s). |
| Weight/packaging unit | 0.5 kg |
| Net weight | 0.47 |
| Gross weight | 0.473 |
| Copper weight (kg per piece) | 0.036 |
| Customs tariff number | 85369095 |
| EAN | 4028177673830 |
| ETIM 7.0 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|--|
| Approvals | ABS DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |