

# Rittal – The System.

Faster – better – everywhere.



## KEL 9402.600 Ex Enclosures

State: 2024-09-27 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9402.600 - Ex Enclosures Stainless steel, empty enclosure with hinged door

Ex Housing with Hinged Door, Stainless Steel

## Features

Model No.	KEL 9402.600
Version	Ex Enclosures
Material	Housing: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Carbon steel
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting panel: Zinc-plated
Supply includes	Housing Door Mounting panel
Dimensions	Width: 380 mm Height: 300 mm Depth: 155 mm
Dimensions of mounting plate (W x H)	334 mm x 275 mm
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Base material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam No. of locks: 1 Lock Insert: 3 mm double-bit
Protection category IP to IEC 60529	IP 66
Protection category NEMA	NEMA 4X

# Features

---

Type rating according to UL 50E	Type 1 Type 4 Type 4X Type 12
---------------------------------	--

---

Packaging unit	1 pc(s).
----------------	----------

---

Weight/packaging unit	7.8 kg
-----------------------	--------

---

Net weight	7.12
------------	------

---

Gross weight	7.26
--------------	------

---

Customs tariff number	94032080
-----------------------	----------

---

EAN	4028177138711
-----	---------------

---

ETIM 7.0	EC002503
----------	----------

---

ECLASS 8.0	27180502
------------	----------

---

# Approvals

---

Approvals	ATEX CQC-CCC IEC Ex UL + C-UL (listed)
-----------	---

---

Explanations	Manufacturer's declaration
--------------	----------------------------

---