

# Rittal – The System.

Faster – better – everywhere.



## AX 1013.000

## Basic enclosure AX, stainless steel

State: 19/10/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 1013.000 - Basic enclosure AX, stainless steel

The robust stainless steel enclosure features an integral locator system, enabling fast, easy, reliable and extensive system configuration with no drilling required.



## Features

Model No.	AX 1013.000
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s), opening angle 130° Mounting plate Lock: 3 mm double-bit
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 4X NEMA 12
Protection category to IEC 60 529	IP 66
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
IK Code	IK10

# Features

Dimensions	Width: 500 mm Height: 500 mm Depth: 300 mm
Material thickness - enclosure	1.25 mm
Material thickness of mounting plate	2.5 mm
Dimensions mounting plate (W x H)	450 mm x 475 mm
Number of doors	1
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit Material lock: Die-cast zinc
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).
Weight/pack	16.6 kg
Net weight	16
Gross weight	16.6
PCF/PU (cradle-to-gate)	74.4 kg CO2 eq (Cat B)
Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	94032080
EAN	4028177815131
E-Number Sweden	E3465129
ETIM 8	EC000261
ETIM 7.0	EC000261
ECLASS 8.0	27180101

# Approvals

---

Approvals	Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

---

## Tender text

Enclosure (compact enclosure, stainless steel)

Enclosure with door:

Stable stainless steel construction

consisting of body folded from a single piece and welded,  
with protection channel all-round door opening,  
solid rear panel with knockouts for attaching  
wall mounting brackets.

Door with foamed-in PU seal,  
screw-fastened hinges.

Right-hand hinge may be swapped to the left,

130° opening angle to VDI,

earthing bolt, integral enclosure bosses for interior installation,

two cam locks with double-bit insert to DIN 43668

Mounting plate: With machined keyholes for earthing,  
with imprinted scale, attached with Limbach nuts.

QR code:

QR code printed on body, cover and rating plate  
for clear identification and easy retrieval of relevant  
product information and documentation,  
and for clear traceability of the individual parts.

Accessories: Mini-comfort handle, lock inserts,  
wall mounting bracket, earth straps, perforated door strip,  
wiring plan pockets, door stay, viewing window,  
operating panels, fan-and-filter units, heaters,  
swing frame, protective roof.

Material:

Enclosure, door: Stainless steel 1.4301 (AISI 304)

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

Brushed, grain size 400

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4X

Dimensions (W x H x D): 500x500x300 mm

Dimensions mounting plate (W x H): 450 x 475 mm

Model No.:1013.000

Manufacturer: Rittal GmbH & Co. KG