


Rittal – The System.

Faster – better – everywhere.



SV 9681.204

Perforated mounting strip

State: 2024-10-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9681.204 - Perforated mounting strip for partial door

For retro-fitting to partial doors, with 25 mm hole pattern for individual mountings on the rear of the door, e.g. cable ducts, conduit holders etc.



Features

Model No.	SV 9681.204
Product description	For retrofitting to partial doors. The perforated mounting strips have a 25 mm hole pattern and can be used for individual attachments such as cable ducts, hose holders, etc., and are used on the back of the doors. Hole diameter of the perforated mounting strip: 4.5 mm.
Material	Carbon steel, 1 mm
Surface finish	Zinc-plated
Supply includes	Assembly components
Length	198 mm
Mounting tip	For enclosure width 1000 mm: 1 x 9681.204 and 1 x 9681.206
Dimensions	Length: 198 mm
Suitable for	Width: 400 mm
OUT_SUITABLE_FOR_PARTIAL_DOOR_HEIGHTS	200 - 800 mm
Packaging unit	10 pc(s).
Weight/packaging unit	0.64 kg
Net weight	0.6
PCF/PU (cradle-to-gate)	2.4 kg CO2 eq (Cat B)

Features

Note on the PCF class	Category B: PCF value (cradle-to-gate) approximated based on product weight and self-declared
Customs tariff number	73269098
EAN	4028177930353
ETIM 7.0	EC000386
ECLASS 8.0	27400501

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---