

Rittal – The System.

Faster – better – everywhere.



AX 1073.000

Basic enclosure AX, sheet steel

State: 01/09/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1073.000 - Basic enclosure AX, sheet steel

The compact enclosure AX with integral enclosure locators in the roof, base and side forms the familiar 25 mm system pitch pattern from the VX25 large enclosure. With this unique, patented system, AX compact enclosures are prepared for all types of configurations and refits. System components and accessories are easily, quickly and securely installed and retrofitted on rails, with no drilling required.

Features

Model No.	AX 1073.000
Benefits	<p>More interior installation options thanks to integral enclosure locators on a 25 mm system pitch pattern combined with the interior installation rail and our diverse range of system accessories</p> <p>Maintains the protection category (UL approval) by mounting the interior installation rail with no drilling required.</p> <p>Base configuration rail provides additional mounting level and increased load capacity</p> <p>Simple planning and configuration with the Rittal RiPanel configurator</p>
Material	<p>Enclosure: Sheet steel</p> <p>Door: Sheet steel, all-round foamed-in PU seal</p>
Surface finish	<p>Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint</p> <p>Mounting plate: Zinc-plated</p>
Colour	RAL 7035
Supply includes	<p>Enclosure with door(s)</p> <p>Gland plate(s) in enclosure base</p> <p>Mounting plate</p> <p>Perforated door strip</p> <p>Lock: 3 mm double-bit</p>
Protection category NEMA	<p>NEMA 1</p> <p>NEMA 3R</p> <p>NEMA 4</p> <p>NEMA 12</p>
Protection category to IEC 60 529	IP 66

Features

Type rating to UL 50E	Type 1 Type 3R Type 4 Type 12
IK Code	IK10
Dimensions	Width: 760 mm Height: 760 mm Depth: 300 mm
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness of mounting plate	2.5 mm
Dimensions mounting plate (W x H)	705 mm x 735 mm
Number of doors	1
Interchangeable door hinge	Yes
Number of locks	2
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit
Gland plate	Size: 5 Qty.: 2
Basic material	Sheet steel
Packs of	1 pc(s).
Weight/pack	40.5 kg
Customs tariff number	94032080
EAN	4028177813267
E-Number Sweden	E3465150
ETIM 8	EC000261
ETIM 7.0	EC000261

Features

ECLASS 8.0

27180101

Approvals

Approvals

Bureau Veritas
DNV-GL
Lloyds Register of Shipping
UL + C-UL (listed)

Explanations

Manufacturer's declaration
Declaration of conformity
Declaration of conformity UK

Tender text

Enclosure (compact enclosure)

Enclosure with door:

Stable sheet steel construction consisting of body folded from a single piece and welded, with protection channel all-round door opening, rear panel with eyelets for wall mounting bracket.

Enclosure base with sheet steel gland plate.

Door with foamed-in PU seal, vertical perforated door strip on both sides, with PE conductor connection, screw-fastened hinges.

Right-hand hinge may be swapped to the left, 130° opening angle to VDI (may be retrofitted to 180°), two cam locks with double-bit insert to DIN 43668.

Mounting plate: With machined keyholes for earthing, with imprinted scale, attached with ring nuts.

QR code:

QR code printed on body, cover and rating plate for clear identification and easy retrieval of relevant

product information and documentation,
and for clear traceability of the individual parts.

Accessories: Comfort handle, lock inserts,
wall mounting bracket,
plastic and metal gland plates,
modular cable entry, earth straps,
wiring plan pockets, door stay, viewing window,
operating panels, fan-and-filter units, heaters,
swing frame, protective roof, 180° hinge

Material:

Enclosure, door: Sheet steel

Mounting plate: Sheet steel, zinc-plated

Enclosure and door surface finish:

Triple surface treatment for optimum protection
against corrosion and resistance to mineral oils,
lubricants, machining emulsions and solvents:

Nanoceramic coating, electrophoretic dipcoat priming

Powder-coated on the outside in textured RAL 7035.

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4

Dimensions (W x H x D): 760x760x300 mm