


# Rittal – The System.

Faster – better – everywhere.



## AE 1015.600

## Compact enclosures AE

State: 29/06/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1015.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

## Features

Model No.	AE 1015.600
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 400 mm Height: 500 mm Depth: 210 mm
Dimensions mounting plate (W x H)	354 mm x 475 mm
Number of doors	1
Number of locks	2
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).

# Features

---

Weight/pack	12.9 kg
Customs tariff number	94032080
EAN	4028177583917
E-Number Sweden	E3404511
ETIM 7.0	EC000261
ECLASS 8.0	27180101

# Approvals

---

Approvals	DNV-GL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK