


# Rittal – The System.

Faster – better – everywhere.



## KX 1514.000

### Terminal box KX, sheet steel, without gland plate

State: 23/11/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1514.000 - Terminal box KX, sheet steel, without gland plate

The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | KX 1514.000  |
| Product description               | The small enclosure KX, terminal box KX, without a gland plate allows for flexible interior installation while maintaining a high protection category. |
| Material                          | Enclosure: Sheet steel<br>Cover: Sheet steel, all-round foamed-in PU seal  |
| Surface finish                    | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint  |
| Colour                            | RAL 7035   |
| Supply includes                   | Enclosure with cover<br>Mini cam lock  |
| Protection category NEMA          | NEMA 1<br>NEMA 3R<br>NEMA 4<br>NEMA 12   |
| Protection category to IEC 60 529 | IP 66  |
| Type rating to UL 50E             | Type 1<br>Type 3R<br>Type 4<br>Type 12   |
| IK Code                           | IK08   |
| Dimensions                        | Width: 150 mm<br>Height: 150 mm<br>Depth: 80 mm  |
| Material thickness - cover        | 1.25 mm  |

# Features

---

|                                |  |
|--------------------------------|--|
| Material thickness - enclosure | 1.25 mm  |
| Basic material                 | Sheet steel  |
| Packs of                       | 1 pc(s).   |
| Weight/pack                    | 1.21 kg  |
| Net weight                     | 1.012  |
| Gross weight                   | 1.207  |
| PCF per pack (cradle-to-gate)  | 5.9 kg CO2 eq (Cat B)  |
| Note on PCF category           | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number          | 84879090   |
| EAN                            | 4028177816282  |
| E-Number Sweden                | E3465194   |
| ETIM 8                         | EC000261   |
| ETIM 7.0                       | EC000261   |
| ECLASS 8.0                     | 27180101   |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | Bureau Veritas<br>DNV-GL<br>Lloyds Register of Shipping<br>UL + C-UL (listed)           |
| Certificates | Protection category   |
| Explanations | Manufacturer's declaration<br>Declaration of conformity<br>Declaration of conformity UK |

# Tender text

Enclosure (terminal box without gland plate)

Enclosure with cover:

Stable sheet steel design,  
body folded from a single piece and welded,  
with protection channel all-round cover opening,  
rear panel with eyelets for wall mounting bracket,  
cover with foamed-in PU seal,  
with PE conductor connection in the enclosure  
and via U-shaped bracket in the cover,  
for quick and easy earthing,  
with mini cam lock.

QR code:

QR code printed on body, cover and rating plate  
for clear identification and easy retrieval of relevant  
product information and documentation,  
and for clear traceability of the individual parts.

Accessories: Cover hinge, cover retainer, mounting plate,  
top hat rail, wall mounting bracket,  
mounting claw for second mounting level.

Material:

Enclosure, cover: Sheet steel

Surface finish:

Triple surface treatment for optimum protection  
against corrosion and resistance to mineral oils,  
lubricants, machining emulsions and solvents:  
Nanoceramic coating, electrophoretic dipcoat priming  
Powder-coated on the outside in textured RAL 7035.

Protection category to IEC 60 529: IP 66

Protection category to UL 508A: Type 4

Dimensions (W x H x D): 150x150x80 mm