


Rittal – The System.

Faster – better – everywhere.



SK 3138.000

Roof-mounted fan, roof vent

State: 19/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3138.000 - Roof-mounted fan, roof vent

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories. Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.

Features

| | |
|-------------------------------------|---|
| Model No. | SK 3138.000 |
| Design | roof-mounted |
| Product description | Roof-mounted fan with a high protection category and flexible installation from the inside or outside. |
| Colour | RAL 7035 |
| Supply includes | Complete unit ready to install, including pleated filter |
| Fan | without fan motor |
| Dimensions | Width: 400 mm Height: 133 mm Depth: 400 mm |
| Installation depth | 27.5 mm |
| Mounting cut-out | Cut-out width: 258 mm Cut-out depth: 258 mm |
| IP protection category to IEC 60529 | IP 21 without filter mat IP 54 including pleated filter |
| Protection category NEMA | NEMA 12 |
| Note | A chopped-fibre filter filter may optionally be used to increase the protection category to IP55 (see accessories). To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| Operating temperature range | -20 °C...55 °C |
| Storage temperature range | -40 °C...70 °C |

Features

| | |
|-----------------------|---------------|
| Weight/pack | 3.2 kg |
| Packs of | 1 pc(s). |
| Net weight | 3.2 |
| Gross weight | 3.5 |
| Customs tariff number | 84213925 |
| EAN | 4028177709188 |
| ETIM 8 | EC000320 |
| ETIM 7.0 | EC000320 |
| ECLASS 8.0 | 27180716 |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

Roof-mounted fan, roof vent

SK 3138.000

The new generation of roof-mounted fans is one system for all sizes: only one mounting cut-out is needed for all output categories.

Air routing with minimal pressure losses ensures a high level of efficiency, while an innovative clamping attachment supports a high protection category of IP54.

Colour: RAL 7035

Supply includes: Complete unit ready to install, including pleated filter

Fan: without fan motor

Dimensions (WxHxD): 400x133x400 mm

Mounting cut-out (WxD): 258x258 mm

Installation depth: 27.5 mm

IP protection category to IEC 60 529:

IP21 without filter mat, IP54 including pleated filter

Protection category NEMA: NEMA 12

Operating temperature range: -20 °C to 55 °C

Storage temperature range: -40 °C to 70 °C

Weight/pack: 3.2 kg