


# Rittal – The System.

Faster – better – everywhere.



## SK 3238.400 Blue e+ outlet filter

State: 17/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3238.400 - Blue e+ outlet filter EMC

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



## Features

Model No.	SK 3238.400
Design	EMC
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Tool-free assembly
Colour	RAL 7035
Supply includes	Outlet filter EMC filter mat
Mounting cut-out	Cut-out width: 124 mm Cut-out height: 124 mm
To fit Model No.	SK 3238.8xx
Dimensions	Width: 148.5 mm Height: 148.5 mm Depth: 34.2 mm
Protection category NEMA	Type 12 with chopped-fibre filter Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood
IP protection category to IEC 60529	IP54 with chopped-fibre filter IP56 with chopped-fibre filter and hose-proof hood
Weight/pack	0.17 kg
Packs of	1 pc(s).

# Features

---

Customs tariff number	39269097
EAN	4028177998407
ETIM 8	EC002513
ETIM 7.0	EC002513
ECLASS 8.0	27180706

# Approvals

---

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--