


Rittal – The System.

Faster – better – everywhere.



SK 3239.308 Blue e+ outlet filter

State: 17/09/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.308 - Blue e+ outlet filter

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

Model No.	SK 3239.308
Design	wall-mounted
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Tool-free assembly
Colour	RAL 9005
Supply includes	Outlet filter Pleated filter
Mounting cut-out	Cut-out width: 177 mm Cut-out height: 177 mm
To fit Model No.	SK 3239.7xx
Dimensions	Width: 204 mm Height: 204 mm Depth: 45.8 mm
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped-fibre filter/pleated filter and hose-proof hood

Features

IP protection category to IEC 60529	IP54 with chopped-fibre filter/pleated filter IP55 with pleated filter and absorber mat IP56 with chopped-fibre filter/pleated filter and hose-proof hood
Weight/pack	0.39 kg
Packs of	1 pc(s).
Customs tariff number	39269097
EAN	4028177998384
ETIM 8	EC002513
ETIM 7.0	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--
