

Rittal – The System.

Faster – better – everywhere.



SK 3239.400 Blue e+ outlet filter

State: 18/07/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.400 - Blue e+ outlet filter EMC

For ventilation by convection, an outlet filter can be fitted in both the upper and lower sections of the enclosure.



Features

Model No.	SK 3239.400
Design	EMC
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Tool-free assembly
Colour	RAL 7035
Supply includes	Outlet filter EMC filter mat
Mounting cut-out	Cut-out width: 177 mm Cut-out height: 177 mm
To fit Model No.	SK 3239.8xx
Dimensions	Width: 204 mm Height: 204 mm Depth: 45.8 mm
Protection category NEMA	Type 12 with chopped-fibre filter Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood
IP protection category to IEC 60529	IP54 with chopped-fibre filter IP56 with chopped-fibre filter and hose-proof hood
Weight/pack	0.39 kg
Packs of	1 pc(s).

Features

Customs tariff number	39269097
EAN	4028177998377
ETIM 8	EC002513
ETIM 7.0	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--