


Rittal – The System.

Faster – better – everywhere.



SV 3427.010

Bus-mounting fuse base

State: 17/07/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3427.010 - Bus-mounting fuse base

3-pole, for 60 mm bar centre distance.

Features

Model No.	SV 3427.010
Material	Bus-mounting fuse base: Fibreglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to-centre spacing	60 mm
Type of electrical connection	Box terminal
Fuse inserts	D II-E 27 (adaptor screw)
Rated insulation voltage	690 V
Rated current max.	25 A
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 42 mm Height: 209 mm
Connection for round conductor cross-sections	1.5 - 16 mm ²
To fit busbars	Height: 5, 10 mm
Rated operating voltage	500 V (DC) 500 V, 3~
Number of poles	3-pole
Rated operating voltage (L1 + L2)	500 V (DC)
Rated operating voltage (L1 + L3)	500 V (DC)
Packs of	10 pc(s).

Features

Weight/pack	2.47 kg
Copper weight (kg per piece)	0.046
Customs tariff number	85369095
EAN	4028177674950
ETIM 7.0	EC001644
ECLASS 8.0	27142120

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity