


Rittal – The System.

Faster – better – everywhere.



AS 4055.470 Hole punch, sub-D

State: 07/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.470 - Hole punch, sub-D for sheet steel and stainless steel

For punching rectangular cut-outs for connectors

Features

Model No.	AS 4055.470
Product description	For punching rectangular cut-outs for connectors. The hole punch is operated with a wrench or hydraulic punch.
Benefits	With side ejector for the waste No jamming of the die Anti-twist axles for stamps and dies are used as tension bolts.
Supply includes	Female dies Male dies Tension bolts Lock nut Pressure nut with ball bearing Adaptor for hydraulics Plastic case
Maximum machinable material thickness, stainless steel	1.5 mm
Maximum machinable material thickness, sheet steel	2 mm
□ punch	19.8 x 11.3 mm
Packs of	1 pc(s).
Weight/pack	0.466 kg
Net weight	0.466
Gross weight	0.648
Customs tariff number	82073010
EAN	4028177808553
ETIM 7.0	EC000156

Features

ECLASS 8.0

21049047