

# Rittal – The System.

Faster – better – everywhere.



## VX\_IT 5302.154

## 482.6 mm (19") mounting angles, dynamic

State: 02/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# VX\_IT 5302.154 - 482.6 mm (19") mounting angles, dynamic for VX IT

Mounting angles, also for accommodating server system installation kits.

## Features

Model No.	VX IT 5302.154
Product description	Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design can directly accommodate all commercially available mounting kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings.
Benefits	Integral, bidirectional U labelling Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling
Technical specifications	Side punchings, round and square, on a U pitch pattern Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components 482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E
Applications	For mounting a 482.6 mm (19") mounting level within the VX IT rack system
Material	Sheet steel, 2.5 mm
Surface finish	Primed
Colour	RAL 9005
Supply includes	Assembly parts
Mounting position	front
Installation options	Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected

# Features

---

Assembly instruction	To be combined with cross-member, depth stays or mounting bracket for attachment Use of the different mounting options depends on the relevant enclosure dimensions
To fit	Height: = 42 U
Packs of	2 pc(s).
Weight/pack	12.04 kg
Customs tariff number	73269098
EAN	4028177955554
ETIM 7.0	EC002620
ECLASS 8.0	27189261

---