

Rittal – The System.

Faster – better – everywhere.



AS 4055.212 Hole punch, round

State: 27/09/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.212 - Hole punch, round for sheet steel

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.212 |
| Design | With 3 cutting points |
| Supply includes | Female dies Male dies Tension screw without ball bearing |
| Maximum machinable material thickness, sheet steel | 2 mm |
| Ø punch | 12.7 mm |
| For threads | M12 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number | 4055.661 |
| Tension screw (Ø x L) | 9.5 x 50 mm |
| Hydraulic tension screw Ø | 9.5 mm 19 mm |
| Packs of | 1 pc(s). |
| Weight/pack | 0.065 kg |
| Net weight | 0.065 |
| Gross weight | 0.08 |
| Customs tariff number | 82073010 |
| EAN | 4028177808188 |
| ETIM 8 | EC000156 |
| ETIM 7.0 | EC000156 |

Features

ECLASS 8.0

21049047