

Rittal – The System.

Faster – better – everywhere.



AS 4055.232 Hole punch, round

State: 19/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.232 - Hole punch, round for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.232
Design	With 3 cutting points
Supply includes	Female dies Male dies Tension screw without ball bearing
Maximum machinable material thickness, sheet steel	2 mm
Ø punch	32.5 mm
For threads	M32
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.661
Tension screw (Ø x L)	9.5 x 50 mm
Hydraulic tension screw Ø	9.5 mm 19 mm
Packs of	1 pc(s).
Weight/pack	0.219 kg
Net weight	0.219
Gross weight	0.242
Customs tariff number	82073010
EAN	4028177808270
ETIM 8	EC000156
ETIM 7.0	EC000156

Features

ECLASS 8.0

21049047