

Rittal – The System.

Faster – better – everywhere.



AS 4055.247 Hole punch, round

State: 07/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.247 - Hole punch, round for sheet steel

For punching round cut-outs

Features

Model No.	AS 4055.247
Design	With 3 cutting points
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	Female dies Male dies Tension screw without ball bearing
Maximum machinable material thickness, sheet steel	3 mm
Ø punch	47 mm
Note	When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Weight/pack	0.687 kg
Net weight	0.687
Gross weight	0.728
Customs tariff number	82073010
EAN	4028177808324
ETIM 8	EC000156
ETIM 7.0	EC000156

Features

ECLASS 8.0

21049047