

Rittal – The System.

Faster – better – everywhere.



AS 4055.474 Hole punch, sub-D

State: 07/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.474 - Hole punch, sub-D for sheet steel and stainless steel

For punching rectangular cut-outs for connectors

Features

| | |
|--|---|
| Model No. | AS 4055.474 |
| Product description | For punching rectangular cut-outs for connectors. The hole punch is operated with a wrench or hydraulic punch. |
| Benefits | With side ejector for the waste No jamming of the die Anti-twist axles for stamps and dies are used as tension bolts. |
| Supply includes | Female dies Male dies Tension bolts Lock nut Pressure nut with ball bearing Adaptor for hydraulics Plastic case |
| Maximum machinable material thickness, stainless steel | 1 mm |
| Maximum machinable material thickness, sheet steel | 1.65 mm |
| □ punch | 55.7 x 13.9 mm |
| Packs of | 1 pc(s). |
| Weight/pack | 0.89 kg |
| Net weight | 0.89 |
| Gross weight | 0.903 |
| Customs tariff number | 82073010 |
| EAN | 4028177808591 |
| ETIM 8 | EC000156 |

Features

| | |
|----------|----------|
| ETIM 7.0 | EC000156 |
|----------|----------|

| | |
|------------|----------|
| ECLASS 8.0 | 21049047 |
|------------|----------|