

# Rittal – The System.

Faster – better – everywhere.



## DK 7030.501 Door control module

State: 17/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7030.501 - Door control module

Control unit for automatic opening of glazed doors VX IT for ADO with integral vent flaps.

## Features

Model No.	DK 7030.501
Product description	Control unit for automatic opening of glazed doors VX IT for ADO with integral vent flaps. Designed for a rack with front and rear door. To fit CMC III system with CAN bus.
Technical specifications	Maximum no. of PU : 16 Maximum no. of PU Compact: 4 1st rated voltage: 24 V (DC) 7030.060 for door control module and glazed doors VX IT for ADO, redundant to 2nd rated voltage 2nd rated voltage: 24 V (DC) 7030.060 for door control module and glazed doors VX IT for ADO 1 x temperature sensor input 3 x digital inputs: Alarm/front door flaps/rear door flaps 1 x input for reader units: Combination lock/transponder reader for local function testing of the vent flaps 2 x outputs for glazed doors VX IT for ADO with integral vent flaps, magnetic system with damper integrated into the door 2 x CAN bus CMC III: RJ45 for CAN bus cable
Material	Plastic
Colour	Front: RAL 9005 Enclosure: RAL 7035
Supply includes	Basic system Temperature sensor including connection cable (supplied loose) Assembly parts for mounting on surfaces
Packs of	1 pc(s).
Weight/pack	0.66 kg
Customs tariff number	90330090
EAN	4028177951570
ETIM 7.0	EC001770

# Features

---

ECLASS 8.0

27390190

# Approvals

---

Approvals

UL + C-UL (listed)

Explanations

Manufacturer's declaration  
Declaration of conformity