

# Rittal – The System.

Faster – better – everywhere.



## VX 8620.063

# Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm, stainless steel

State: 26/09/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8620.063 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 200 mm, stainless steel

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

## Features

|                     |  |
|---------------------|--|
| Model No.           | VX 8620.063  |
| Product description | Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover. |
| Material            | Base/plinth corner piece: Stainless steel 1.4301 (AISI 304)<br>Base/plinth trim panel front/rear: Stainless steel 1.4301 (AISI 304)<br>Corner and baying cover: Plastic  |
| Surface finish      | Trim panel: Brushed, grain size 400  |
| Supply includes     | 4 base/plinth corner pieces<br>4 corner covers<br>1 baying cover<br>1 base/plinth trim panel, front/rear, 200 mm high<br>2 base/plinth trim panels, front/rear, 100 mm high<br>Assembly parts  |
| Note                | Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth<br>Components of the 1st generation of the base/plinth system cannot be combined with components of the 2nd generation           |
| Dimensions          | Height: 200 mm   |
| To fit              | Width: = 1,200 mm  |

# Features

---

|                       |   |
|-----------------------|---|
| Type rating to UL 50E | Type 1<br>Type 3R<br>Type 4<br>Type 4X<br>Type 12 |
|-----------------------|---|

---

|             |         |
|-------------|---------|
| Weight/pack | 15.2 kg |
|-------------|---------|

---

|          |          |
|----------|----------|
| Packs of | 2 pc(s). |
|----------|----------|

---

|            |       |
|------------|-------|
| Net weight | 11.22 |
|------------|-------|

---

|              |       |
|--------------|-------|
| Gross weight | 11.35 |
|--------------|-------|

---

|                       |          |
|-----------------------|----------|
| Customs tariff number | 94039910 |
|-----------------------|----------|

---

|     |               |
|-----|---------------|
| EAN | 4028177922365 |
|-----|---------------|

---

|          |          |
|----------|----------|
| ETIM 7.0 | EC000721 |
|----------|----------|

---

|            |          |
|------------|----------|
| ECLASS 8.0 | 27182003 |
|------------|----------|

---

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|