

Rittal – The System.

Faster – better – everywhere.



KEL 9306.000 Ex enclosures

State: 22/12/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9306.000 - Ex enclosures Stainless steel, empty enclosure with screw fastened cover

Ex enclosure with screw-fastened cover, stainless steel

Features

Model No.	KEL 9306.000
Design	Ex enclosures
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Enclosure Cover
Dimensions	Width: 300 mm Height: 300 mm Depth: 120 mm
Certificate IEC EX PTB 09.0033U	Yes
Certificate PTB 03 ATEX 1013U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
IP protection category to IEC 60529	IP 66
Packs of	1 pc(s).
Net weight	3.7
Gross weight	3.9
Customs tariff number	94032080
EAN	4028177138643
ETIM 9	EC002503
ECLASS 8.0	27180502

Approvals

Approvals

ATEX
CQC-CCC
IEC Ex
UL + C-UL (listed)