


# Rittal – The System.

Faster – better – everywhere.



## SV 9342.504

# Circuit-breaker component adaptor

State: 17/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9342.504 - Circuit-breaker component adaptor 4-pole

## Features

Model No.	SV 9342.504
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	Terminal cover Sliding blocks
Type of electrical connection	Box terminal
Rated current max.	160 A
Rated operating voltage	690 V, 4~
Electrical ratings UL (SCCR)	65 kA - 480 V, circuit breaker max. 125 A, DIVQ/7
Cable outlet	Top
For bar systems with centre-to-centre spacing	60 mm
Note	Cable outlet: Switch outlet or as outgoing cable from the switchgear The technical data may vary for UL applications
Number of poles	4-pole
Dimensions	Width: 120 mm Height: 277 mm
Connection for round conductor cross-sections	35 - 120 mm <sup>2</sup>
Clamping area for laminated copper bars (W x H)	18.5 x 15.5 mm
To fit busbars	Height: 5, 10 mm

# Features

---

To fit manufacturer (model)	ABB (T1, T2, XT1, XT2) Eaton (NZM1-4/125 A, BZM E1-4/100 A) Schneider Electric (NSC100) Schrack (MC1) Siemens (3VA10, 3VA11)
Packs of	1 pc(s).
Weight/pack	1.425 kg
Copper weight (kg per piece)	0.258
Customs tariff number	85369095
EAN	4028177551756
ETIM 7.0	EC001531
ECLASS 8.0	27370304

# Approvals

---

Approvals	ABS C-UL Lloyds Register of Shipping UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK