

Rittal – The System.

Faster – better – everywhere.



SV 9343.030

NH fuse-switch-disconnectors, size 00 to 3

State: 19/10/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9343.030 - NH fuse-switch-disconnectors, size 00 to 3 with electronic fuse monitoring

Features

Model No.	SV 9343.030
Material	Polyamide Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Clamping area for laminated copper bars	Clamping area width: 20 mm Clamping area height: 5 mm
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Screw M8
Rated operating current max.	160 A
For NH size	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 106 mm Height: 194 mm
Connection for round conductor cross-sections	10 - 95 mm ²
To fit busbars	Height: 5, 10 mm
Rated operating voltage	400 V - 690 V, 3~
Number of poles	3-pole
Packs of	1 pc(s).
Weight/pack	1.027 kg

Features

Net weight	0.927
Gross weight	1.029
Copper weight (kg per piece)	0.2
Customs tariff number	85369095
EAN	4028177540293
ETIM 7.0	EC001040
ECLASS 8.0	27371401

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK