


# Rittal – The System.

Faster – better – everywhere.



## SV 9344.110

# NH fuse-switch-disconnectors, size 00 to 3

State: 17/07/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9344.110 - NH fuse-switch-disconnectors, size 00 to 3

## Features

|   |   |
|---|---|
| Model No.                                     | SV 9344.110   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated             |
| Colour  | Chassis: RAL 7035<br>Cover: RAL 7035/7001   |
| Clamping area for laminated copper bars       | Clamping area width: 32 mm<br>Clamping area height: 10 mm   |
| for mounting plate assembly                   | Yes   |
| Cable outlet                                  | Top/bottom  |
| Type of electrical connection                 | Screw M10   |
| Rated operating current max.                  | 250 A   |
| For NH size                                   | 1   |
| Note  | The technical data may vary for UR applications. Applications to UR only in conjunction with "Special Purpose Fuses". |
| Test specification                            | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)   |
| Dimensions                                    | Width: 184 mm<br>Height: 298 mm   |
| Connection for round conductor cross-sections | 10 - 150 mm <sup>2</sup>  |
| Rated operating voltage                       | 690 V, 3~   |
| Number of poles                               | 3-pole  |
| Packs of                                      | 1 pc(s).  |
| Weight/pack                                   | 2.14 kg   |
| Copper weight (kg per piece)                  | 0.3   |

# Features

---

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 85365080      |
| EAN                   | 4028177540606 |
| ETIM 7.0              | EC001040      |
| ECLASS 8.0            | 27371401      |

---

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | C-UR<br>CQC-CCC<br>UR + C-UR (recognized)                 |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---