

# Rittal – The System.

Faster – better – everywhere.



## PK 9508.000

## Polycarbonate enclosures PK

State: 23/04/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9508.000 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

Model No.	PK 9508.000
Design	PK enclosure with solid cover
Product description	Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.
Material	Enclosure: Fibreglass-reinforced polycarbonate Cover grey: Fibreglass-reinforced polycarbonate, all-round foamed-in PU seal Cover screws: Polyamide Insulating bungs: Polyethylene
Colour	RAL 7035
Supply includes	Enclosure with cover Cover screws Insulating bungs for wall mounting screws
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08

# Features

---

Dimensions	Width: 130 mm Height: 94 mm Depth: 57 mm
------------	--

---

Operating temperature range	-35 °C...80 °C
-----------------------------	----------------

---

Basic material	Polycarbonate
----------------	---------------

---

Packs of	4 pc(s).
----------	----------

---

Net weight	0.8
------------	-----

---

Gross weight	0.898
--------------	-------

---

Customs tariff number	94037000
-----------------------	----------

---

EAN	4028177139251
-----	---------------

---

ETIM 9	EC000261
--------	----------

---

ECLASS 8.0	27180101
------------	----------

# Approvals

---

Approvals	C-UL DNV-GL UL UL + C-UL (listed)
-----------	--

---

Explanations	Declaration of conformity
--------------	---------------------------