

# Rittal – The System.

Faster – better – everywhere.



## KEL 9405.600 Ex enclosures

State: 19/10/2024 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9405.600 - Ex enclosures Stainless steel, empty enclosure with hinged door

Ex enclosure with hinged door, stainless steel

## Features

Model No.	KEL 9405.600
Design	Ex enclosures
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure Door Mounting plate
Dimensions	Width: 600 mm Height: 600 mm Depth: 210 mm
Dimensions mounting plate (W x H)	549 mm x 570 mm
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam Number of locks: 2 Lock insert: 3 mm double-bit
IP protection category to IEC 60529	IP 66
Protection category NEMA	NEMA 4X

# Features

---

Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12
-----------------------	--

---

Packs of	1 pc(s).
----------	----------

---

Weight/pack	25.2 kg
-------------	---------

---

Net weight	21.94
------------	-------

---

Gross weight	23.5
--------------	------

---

Customs tariff number	94032080
-----------------------	----------

---

EAN	4028177138803
-----	---------------

---

ETIM 7.0	EC002503
----------	----------

---

ECLASS 8.0	27180502
------------	----------

# Approvals

---

Approvals	ATEX CQC-CCC IEC Ex UL + C-UL (listed)
-----------	---

---

Explanations	Manufacturer's declaration
--------------	----------------------------